



i2 Inground

Inground, w/ Stainless Steel Trim Ring, Stainless Steel, 75W MR16, 120V

Inground, w/ Stainless Steel Trim Ring, Stainless Steel, 75W MR16, 120V

The i2 Inground is a line voltage inground luminaire available in halogen, incandescent and LED sources. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. The optical assembly has a clear convex tempered soda-lime glass lens and 358° rotation without interruption of beam pattern.

Product data

General Information	
Lamp Source Code	Quartz
Lamp Watts	75
Number of Lamps	1
Mounting	In Ground
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	75
Product Data	
Order product name	INGROUND,SS RING,75W,12V

EAN/UPC - Product	783352021229
Order code	IT216-SS
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400123104
Net Weight (Piece)	0.001 kg
Catalog Number	IT216-SS
Catalog Number Description	Inground, w/ Stainless Steel Trim Ring, Stainless Steel, 75W MR16, 120V