



i2 Inground

INGR W/GRD/TRANS,12V,75W,MR16

Inground, w/ Composite Rock Guard, Bronze, 75W MR16, 120V

The i2 Inground is a line voltage inground luminaire available in halogen, incandescent and LED sources. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. The optical assembly has a clear convex tempered soda-lime glass lens and 358° rotation without interruption of beam pattern.

Product data

General Information	
Lamp Source Code	Quartz
Lamp Watts	75
Number of Lamps	1
Mounting	In Ground
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	75
Product Data	
Order product name	INGR W/GRD/TRANS,12V,75W,MR16

EAN/UPC - Product	783352007223
Order code	IT216G-H
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400123106
Net Weight (Piece)	0.010 kg
Commercial Code	IT216G-H
Catalog Number Description	Inground, w/ Composite Rock Guard, Bronze, 75W MR16, 120V
Quick Ship	Spec Smart (10 Days) USA