



i2 Inground

Inground, w/ Cast Bronze Rock Guard, Natural Brass, 75W MR16, 120V

Inground, w/ Cast Bronze Rock Guard, Natural Brass, 75W MR16, 120V

The i2 Inground is a line voltage inground luminaire available in halogen, incandescent and LED sources. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. The optical assembly has a clear convex tempered soda-lime glass lens and 358° rotation without interruption of beam pattern.

Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Quartz	Order code	IT216G-N
Lamp Watts	75	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Mounting	In Ground	Material Nr. (12NC)	912400123111
Operating and Electrical		Net Weight (Piece)	2.168 kg
Voltages	120 V	Catalog Number	IT216G-N
Luminaire Input Watts	75	Catalog Number Description	Inground, w/ Cast Bronze Rock Guard, Natural Brass, 75W MR16, 120V
Product Data			
Order product name	INGROUND,CAST BRZ RK GRD,12V		