



RFL1 Steplight

STEPLYTE, RECESSED, 12V, 12W, W/93

Step Light, Aluminum, Recessed, Black, 12W S-8 (93), 12V

RFL1 step light is a low voltage for wall applications. The die-cast aluminum faceplate includes a galvanized steel, single gang recessed box with stainless steel fasteners. A frosted tempered glass lens is included and lamping requires a 12W maximum S-8 (93) lamp.

Product data

| General Information | | EAN/UPC - Product | |
|--------------------------|------------------------------------|---------------------------------|--|
| Lamp Source Code | Incandescent | Order code | RFL1-A |
| Lamp Watts | 28 | Numerator - Quantity Per Pack | 1 |
| Number of Lamps | 1 | Numerator - Packs per outer box | 2 |
| Mounting | Recessed | Material Nr. (12NC) | 912400125951 |
| Operating and Electrical | | Net Weight (Piece) | 0.010 kg |
| Voltages | 12 V | Commercial Code | RFL1-A |
| Luminaire Input Watts | 28 | Catalog Number Description | Step Light, Aluminum, Recessed, Black, 12W S-8 (93), 12V |
| Product Data | | Quick Ship | - |
| Order product name | STEPLYTE, RECESSED, 12V, 12W, W/93 | | |