



RLL1 Step Light

Step Light, Aluminum, Recessed Louver, Black, 12W S-8 (93), 12V

Step Light, Aluminum, Recessed Louver, Black, 12W S-8 (93), 12V

The low voltage RLL1 step light is a die-cast aluminum faceplate with galvanized steel, single gang recessed box with stainless steel fasteners and diecut neoprene gasket. Lamping specifications is a 12W maximum S-8 lamp with a frosted tempered glass lens.

Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	28
Number of Lamps	1
Mounting	Recessed
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	28
Product Data	
Order product name	STEPLYTE,CAST LVR,12V,12W,W/93

EAN/UPC - Product	783352009081
Order code	RLL1-A
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400126065
Net Weight (Piece)	0.010 kg
Catalog Number	RLL1-A
Catalog Number Description	Step Light, Aluminum, Recessed Louver, Black, 12W S-8 (93), 12V