



RSB2 Step Light

BRICKLYTE,BUBBLE,13W,PLC

Step Light, Polycarbonate, Black, 13W PLC13, 120V

The RSB2 is a polycarbonate step light for line voltage applications. It includes an aluminum back box for concrete and brick applications. The optical assembly consists of a UV stabilized, injection molded polycarbonate bubble faceplate reinforced with frosted tempered glass. A symmetric Reflector is precision formed, semi-specular aluminum or highly polished aluminum, which produces a wide symmetric distribution for general area lighting. Lamping choices include PLC, CFL and incandescent.

Product data

General Information		EAN/UPC - Product	783352010148
Lamp Source Code	Compact Fluorescent	Order code	RSB2AT5F13E
Lamp Watts	28	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Mounting	Recessed	Material Nr. (12NC)	912400126197
Operating and Electrical		Net Weight (Piece)	0.001 kg
Voltages	120 V	Commercial Code	RSB2AT5F13E
Luminaire Input Watts	28	Catalog Number Description	Step Light, Polycarbonate, Black, 13W PLC13, 120V
Product Data		Quick Ship	-
Order product name	BRICKLYTE,BUBBLE,13W,PLC		