



RSB2 Step Light

BRICKLYTE,BUBBLE,120V,40W,T10

Step Light, Polycarbonate, Black, 40W T10, 120V

The RSB2 is a polycarbonate step light for line voltage applications. It includes an aluminum back box for concrete and brick applications. The optical assembly consists of a UV stabilized, injection molded polycarbonate bubble faceplate reinforced with frosted tempered glass. A symmetric Reflector is precision formed, semi-specular aluminum or highly polished aluminum, which produces a wide symmetric distribution for general area lighting. Lamping choices include PLC, CFL and incandescent.

Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	28
Number of Lamps	1
Mounting	Recessed
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	28
Product Data	
Order product name	BRICKLYTE,BUBBLE,120V,40W,T10

EAN/UPC - Product	783352010186
Order code	RSB2AT5IE
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400126202
Net Weight (Piece)	0.010 kg
Commercial Code	RSB2AT5IE
Catalog Number Description	Step Light, Polycarbonate, Black, 40W T10, 120V
Quick Ship	-