



RSB2 Step Light

BRICKLYTE,BUBBLE,120V,13W,PLC

Step Light, Polycarbonate, Bronze, 13W PLC13, 120V

The RSB2 is a polycarbonate step light for line voltage applications. It includes an aluminum back box for concrete and brick applications. The optical assembly consists of a UV stabilized, injection molded polycarbonate bubble faceplate reinforced with frosted tempered glass. A symmetric Reflector is precision formed, semi-specular aluminum or highly polished aluminum, which produces a wide symmetric distribution for general area lighting. Lamping choices include PLC, CFL and incandescent.

Product data

General Information	
Lamp Source Code	Compact Fluorescent
Lamp Watts	28
Number of Lamps	1
Mounting	Recessed

Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	28

Product Data	
Order product name	BRICKLYTE,BUBBLE,120V,13W,PLC

EAN/UPC - Product	783352010223
Order code	RSB2HT5F13E
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400126207
Net Weight (Piece)	0.001 kg
Commercial Code	RSB2HT5F13E
Catalog Number Description	Step Light, Polycarbonate, Bronze, 13W PLC13, 120V
Quick Ship	-