



RSC2 Step Light LED

Step Light, Aluminum, White, 13W PLC13, 120V

Step Light, Aluminum, White, 13W PLC13, 120V

The RSC2 is a line voltage step light perfect for high pedestrian traffic and plant life applications. It is available in standard sources including CFL along with high brightness LED sources. It is available with a die-cast aluminum and bronze construction with low copper to resist corrosion. The cast bronze louver is natural cast bronze with frosted tempered glass. The die-cast copper-free aluminum louver has a 45° cutoff with frosted tempered glass with silicone gasketing. Available in three colors plus natural bronze. Symmetric Reflector is precision formed with a white reflective coating. The cast louver offers lower light levels with cut-off for lighting stairways or general lighting where shielding of the light source is more important than high light levels.

Product data

| General Information | |
|-------------------------------|------------------------|
| Lamp Source Code | Compact Fluorescent |
| Lamp Watts | 28 |
| Number of Lamps | 1 |
| Photometric Distribution Type | General Diffuse |
| Mounting | Recessed |
| Operating and Electrical | |
| Voltages | 120 V |
| Luminaire Input Watts | 28 |
| Product Data | |
| Order product name | LVR BRICKLYTE,120V,13W |

| | |
|---------------------------------|--|
| EAN/UPC - Product | 783352010810 |
| Order code | RSC2BK5F13E |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912400126264 |
| Net Weight (Piece) | 0.010 kg |
| Catalog Number | RSC2BK5F13E |
| Catalog Number Description | Step Light, Aluminum, White, 13W PLC13, 120V |