



RSC2 Step Light LED

LVR BRICKLYTE,120V,40W,T10

Step Light, Aluminum, Bronze, 40W T10, 120V

The RSC2 is a line voltage step light perfect for high pedestrian traffic and plant life applications. It is available in standard sources including CFL along with high brightness LED sources. It is available with a die-cast aluminum and bronze construction with low copper to resist corrosion. The cast bronze louver is natural cast bronze with frosted tempered glass. The die-cast copper-free aluminum louver has a 45° cutoff with frosted tempered glass with silicone gasketing. Available in three colors plus natural bronze. Symmetric Reflector is precision formed with a white reflective coating. The cast louver offers lower light levels with cut-off for lighting stairways or general lighting where shielding of the light source is more important than high light levels.

Product data

| General Information | | EAN/UPC - Product | |
|-------------------------------|----------------------------|---------------------------------|---|
| Lamp Source Code | Incandescent | Order code | RSC2HK5IE |
| Lamp Watts | 28 | Local order code | . |
| Number of Lamps | 1 | Numerator - Quantity Per Pack | 1 |
| Photometric Distribution Type | General Diffuse | Numerator - Packs per outer box | 1 |
| Mounting | Recessed | Material Nr. (12NC) | 912400126294 |
| Operating and Electrical | | Net Weight (Piece) | 0.010 kg |
| Voltages | 120 V | Commercial Code | RSC2HK5IE |
| Luminaire Input Watts | 28 | Catalog Number Description | Step Light, Aluminum, Bronze, 40W T10, 120V |
| Product Data | | Quick Ship | Spec Smart (10 Days) USA |
| Order product name | LVR BRICKLYTE,120V,40W,T10 | | |