



iColor Flex LMX gen2

iColor Flex LMX gen2, Translucent Dome Lens, Black Housing, 12 in On-Center Node Spacing

iColor Flex LMX gen2, Translucent Dome Lens, Black Housing, 12 in On-Center Node Spacing

When designers need high-brightness RGB direct-view accent lighting, or need to design creative low-resolution video displays, iColor Flex LMX gen2 provides flexible strands of large high-intensity LED nodes. Each Flex LMX gen2 node is individually controllable, providing ultimate flexibility of design.

Product data

General Information		Controls and Dimming	
Number of light sources	50 [50 pcs]	Dimmable	Yes
Lamp family code	LED-MD [LED Multi-die]		
Light source colour	RGB	Mechanical and Housing	
Light source replaceable	Yes	Housing material	Polycarbonate
Driver included	No	Optical cover/lens material	Polycarbonate
Optical cover/lens type	TSDM12 [Transparent dome 12 inch separated]	Colour	Black
Luminaire light beam spread	165°	Approval and Application	
CE mark	CE mark	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light Technical		Initial Performance (IEC Compliant)	
Luminous intensity (peak value) on beam axis per node	2.2 cd	Initial luminous flux (system flux)	13 lm
		Initial LED luminaire efficacy	13 lm/W
Operating and Electrical		Initial input power	1 W
Input Voltage	24 V		

iColor Flex LMX gen2

Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 25 °C Calculated	100000
Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 50 °C Calculated	100000
Lumen Maintenance 50% at 50 °C Reported	60000
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	60000


Application Conditions	
Ambient temperature range	-40 to +50 °C

Product Data	
Full product code	871829162311399

Order product name	BGC495 50 RGB TSDM12 BK
EAN/UPC – product	8718291623113
Order code	101-000077-05
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400130027
SAP net weight (piece)	0.980 kg
Commercial Code	101-000077-05
Catalogue number description	iColor Flex LMX gen2, Translucent Dome Lens, Black Housing, 12 in On- Center Node Spacing

IP 66

Dimensional drawing



iColor Flex LMX gen2

