



# Vaya Linear MP

## BCP425 10x50 4000 L1210 CE

Vaya Linear MP is a reliable and cost-effective LED wall grazing luminaire for both interior and exterior use that minimizes initial investment, while offering exceptional flexibility to create eye-catching wall washing and wall grazing effects. A wide range of color and CCT options, in either static on/off or with dynamic color control, adjustable mounting brackets, wide or elliptical beam angles offer a comprehensive toolbox for your facade lighting needs. The discreet design with integrated power supply and waterproof connectors makes wiring simple, fast and reliable.

### Product data

General Information		Mechanical and Housing	
Lamp family code	LED-HB [ LED High Brightness]	Housing Material	Aluminum extruded
Beam angle of light source	10 x 50 °	Optic material	Glass
Light source color	Cool white	Optical cover/lens material	Tempered glass
Light source replaceable	No	Optical cover/lens shape	Flat
Driver included	Yes	Optical cover/lens finish	Clear
Optical cover/lens type	Clear glass	Length	1210 mm
CE mark	CE mark	Color	Dark gray
UL mark	-	Approval and Application	
CQC mark	-	Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Lifetime to 70% luminous flux	60000 h	Mech. impact protection code	IK06 [ 1 J]
PSE mark	PSE mark	Vibration Standard	Complies with ANSI C136.31
Operating and Electrical		Vibration Rating	Complies with ANSI C136.31
Input Voltage	100 to 277 V	Initial Performance (IEC Compliant)	
Input Frequency	50 to 60 Hz	Initial luminous flux (system flux)	3375 lm
Controls and Dimming		Initial luminous flux at color temperature of 4000 K	3375 lm
Dimmable	Yes		

Vaya Linear MP

Initial LED luminaire efficacy	59 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	83
Initial input power	60 W

Over Time Performance (IEC Compliant)

Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	100000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Reported	60000
Lumen Maintenance 80% at 40°C Calculated	100000
Lumen Maintenance 80% at 40°C Reported	60000
Lumen Maintenance 80% at 50°C Calculated	100000
Lumen Maintenance 90% at 25°C Calculated	62000
Lumen Maintenance 90% at 25°C Reported	60000
Lumen Maintenance 90% at 40°C Calculated	62000

Lumen Maintenance 90% at 40°C Reported	60000
--	-------

Application Conditions


Ambient temperature range	-40 to +40 °C
---------------------------	---------------

Product Data

Full product code	871829162574299
Order product name	BCP425 10x50 4000 L1210 CE
EAN/UPC - Product	8718291625742
Order code	912400130124
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400130124
Net Weight (Piece)	3.760 kg



Dimensional drawing



Vaya

