



Vaya Linear MP

BCP425 10x50 5000 L1210 CE

Vaya Linear MP is a reliable and cost-effective LED lighting fixture designed for fixed or dynamic colorful lighting effects. Offering a choice of wide or elliptical beams, Vaya Linear MP is ideal for wall washing and grazing applications. Integrated power and unified power and data connectors make installation fast, easy and reliable.

Product data

| General Information | | | |
|-------------------------------|-------------------------------|--|---|
| Lamp family code | LED-HB [LED High Brightness] | Optic material | Glass |
| Beam angle of light source | 10 x 50 ° | Optical cover/lens material | Tempered glass |
| Light source colour | Cool white | Optical cover/lens shape | Flat |
| Light source replaceable | No | Optical cover/lens finish | Clear |
| Driver included | Yes | Length | 1210 mm |
| Optical cover/lens type | GC [Clear glass] | Colour | Dark gray |
| CE mark | CE mark | Approval and Application | |
| UL mark | - | Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| CQC mark | - | Mech. impact protection code | IK06 [1 J] |
| Lifetime to 70% luminous flux | 60000 h | Initial Performance (IEC Compliant) | |
| PSE mark | PSE mark | Initial luminous flux | 3360 lm |
| Operating and Electrical | | Init. Corr. colour temperature | 5000 K |
| Input voltage | 100 to 277 V | Initial input power | 60 W |
| Input frequency | 50 to 60 Hz | Over Time Performance (IEC Compliant) | |
| Controls and Dimming | | Lumen Maintenance 70% at 25°C Calculated | 100000 |
| Dimmable | Yes | Lumen Maintenance 70% at 25°C Reported | 60000 |
| Mechanical and Housing | | Lumen Maintenance 70% at 40°C Calculated | 100000 |
| Housing material | Aluminum extruded | Lumen Maintenance 70% at 40°C Reported | 60000 |

Vaya Linear MP

| | |
|--|--------|
| Lumen Maintenance 80% at 25°C Reported | 60000 |
| Lumen Maintenance 80% at 40°C Calculated | 100000 |
| Lumen Maintenance 80% at 40°C Reported | 60000 |
| Lumen Maintenance 80% at 50°C Calculated | 100000 |
| Lumen Maintenance 90% at 25°C Calculated | 62000 |
| Lumen Maintenance 90% at 25°C Reported | 60000 |
| Lumen Maintenance 90% at 40°C Calculated | 62000 |
| Lumen Maintenance 90% at 40°C Reported | 60000 |


Application Conditions

| | |
|---------------------------|---------------|
| Ambient temperature range | -40 to +40 °C |
|---------------------------|---------------|


| | |
|---------------------------------|----------------------------|
| Product Data | |
| Full product code | 871829162606099 |
| Order product name | BCP425 10x50 5000 L1210 CE |
| EAN/UPC – product | 8718291626060 |
| Order code | 62606099 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 4 |
| Material no. (12NC) | 912400130156 |
| Net weight (piece) | 3.760 kg |



Dimensional drawing



Vaya



Vaya

