



## Vaya Linear MP, 3000 K, 50°, 0.3 m (1 ft), UL, Landscape Mount

Vaya Linear MP, 3000 K, 50°, 0.3 m (1 ft), UL, Landscape Mount

Vaya Linear MP Landscape is an exterior-rated LED sign lighter solution that minimizes initial investment. Adjustable landscape mounts allow for seamless NPT gland mounting, while the discreet design with integrated power supply ensure simple and reliable wiring.

### Product data

General information		Optical cover/lens finish	
Lamp family code	LED-HB [ LED High Brightness]	Optical cover/lens finish	Clear
Light source color	Neutral white	Length	310 mm
Light source replaceable	No	Color	Dark gray
Driver included	Yes	<b>Approval and application</b>	
Optical cover/lens type	Clear glass	Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Luminaire light beam spread	50°	Mech. impact protection code	IK06 [ 1 J]
UL mark	UL and cUL mark	Vibration Standard	Complies with ANSI C136.31
CQC mark	-	FCC mark	FCC Class A
Lifetime to 70% luminous flux	60000 h	Vibration Rating	Complies with ANSI C136.31
<b>Operating and electrical</b>		<b>Initial performance (IEC compliant)</b>	
Input Voltage	100 to 277 V	Initial luminous flux (system flux)	848 lm
Input Frequency	50 to 60 Hz	Initial LED luminaire efficacy	57.9 lm/W
<b>Controls and dimming</b>		Init. Corr. Color Temperature	3000 K
Dimmable	Yes	Init. Color Rendering Index	78
<b>Mechanical and housing</b>		Initial input power	18 W
Housing Material	Aluminum extruded	<b>Over time performance (IEC compliant)</b>	
Optic material	Glass	Lumen Maintenance 70% at 25°C Calculated	100000
Optical cover/lens material	Tempered glass	Lumen Maintenance 70% at 25°C Reported	60000
Optical cover/lens shape	Flat	Lumen Maintenance 70% at 40°C Calculated	100000

Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Reported	60000
Lumen Maintenance 80% at 40°C Calculated	100000
Lumen Maintenance 80% at 40°C Reported	60000
Lumen Maintenance 80% at 50°C Calculated	100000
Lumen Maintenance 90% at 25°C Calculated	62000
Lumen Maintenance 90% at 25°C Reported	60000
Lumen Maintenance 90% at 40°C Calculated	62000
Lumen Maintenance 90% at 40°C Reported	60000

#### Application conditions

Ambient temperature range	-40 to +40 °C
---------------------------	---------------

#### Product data

Full product code	871829162615299
-------------------	-----------------

Order product name	BCP425 50 3000 L310 UL HMA
EAN/UPC - Product	8718291626152
Order code	350-000023-48
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400130165
Net Weight (Piece)	1.450 kg
Catalog Number	350-000023-48
Catalog Number Description	Vaya Linear MP, 3000 K, 50°, 0.3 m (1 ft), UL, Landscape Mount

