



eColor Reach Powercore gen2

DCP775 RD 100-277V UL CE

Red - 100 to 277 V - 5°

eColor Reach Powercore gen2 high-performance LED luminaires are premium exterior long-throw dynamic high-quality solid color luminaires for lighting tall buildings, bridges, and iconic structures. A full range of accessories allow for customizable beam angles for floodlighting, spotlighting, wall washing, and grazing, along with the efficiency and cost-effectiveness of Powercore technology in a rugged die-cast aluminium housing.

Product data


General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Light source color	Red	Mechanical and Housing	
Light source replaceable	No	Housing Material	Aluminum
Driver included	Yes	Optic material	Glass
Luminaire light beam spread	5°	Approval and Application	
Protection class IEC	Safety class I	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Type description	-	Application Conditions	
CE mark	CE mark	Ambient temperature range	-40 to +50 °C
UL mark	UL mark	Product Data	
Lifetime to 70% luminous flux	70000 h	Full product code	871829162923800
Operating and Electrical		Order product name	DCP775 RD 100-277V UL CE
Input Voltage	100 to 277 V		
Input Frequency	50 to 60 Hz		

eColor Reach Powercore gen2

EAN/UPC - Product	8718291629238
Order code	912400130184
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400130184

Net Weight (Piece)	34.000 kg
--------------------	-----------

Dimensional drawing



Reach

