# **PHILIPS** Lighting



# Vaya Flood HP

## BCP418 48xLED-HB/2700 220-240V 40 CE CQC

48 pcs - LED High Brightness - Medium beam angle 40°

Vaya Flood HP is a reliable and cost effective high output LED flood lighting solution ideal for illuminating large-scale exterior facades, bridges, and monuments. While minimizing initial investment, this Vaya Flood series provides exceptional flexibility to create eye-catching flood, wash and spot lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

#### **Product data**

General Information	
Number of light sources	48 pcs
Lamp family code	LED-HB [ LED High Brightness]
Light source color	Warm white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	Flat glass
Luminaire light beam spread	40°
Protection class IEC	Safety class I
Type description	-
CE mark	CE mark
ENEC mark	ENEC mark
UL mark	-
CQC mark	CQC-mark
Lifetime to 70% luminous flux	50000 h
Optic type outdoor	Medium beam angle 40°
PSE mark	No


RoHS mark	-
WEEE mark	-
Angle	40°
Light Technical	
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Operating and Electrical	
Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Material	Aluminum die cast

### Vaya Flood HP

Optic material	Glass
Optical cover/lens material	Tempered glass
Optical cover/lens shape	Flat
Color	Dark gray
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-
	proof]
Mech. impact protection code	IK06 [ 1 J]
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	9700 lm
Init. Corr. Color Temperature	2700 K
Init. Color Rendering Index	80
Over Time Performance (IEC Complian	t)
Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	60000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	37000

Lumen Maintenance 80% at 40°C Reported	37000
Lumen Maintenance 90% at 25°C Calculated	23000
Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	18000
Lumen Maintenance 90% at 40°C Reported	18000
Application Conditions	
Ambient temperature range	-40 to +40 °C
Product Data	
Full product code	871829163548299
Order product name	BCP418 48xLED-HB/2700 220-240V 40
	CE CQC
EAN/UPC - Product	8718291635482
Order code	912400130403
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400130403
Net Weight (Piece)	7.600 kg

#### **Dimensional drawing**



Vaya



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.