



Vaya Flood HP

BCP418 48xLED-HB/5000 220-240V 10 CE CQC

48 pcs - LED High Brightness - Narrow beam angle 10°

Vaya Flood HP is a reliable and cost-effective white/color-changing floodlight, designed for large-scale exterior installations. The light levels achieved by this compact fixture make it ideal for extensive wall-washing and floodlighting applications – in both static or dynamic colors. Integrated power and DMX512 control make this product easy to use with Philips or third-party DMX controllers.

Product data

General Information		Angle	
Number of light sources	48 [48 pcs]	10°	
Lamp family code	LED-HB [LED High Brightness]	Light Technical	
Light source color	Cool white	Standard tilt angle posttop	0°
Light source replaceable	No	Standard tilt angle side entry	0°
Driver included	Yes	Operating and Electrical	
Optical cover/lens type	FG [Flat glass]	Input Voltage	220 to 240 V
Luminaire light beam spread	10°	Input Frequency	50 to 60 Hz
Protection class IEC	Safety class I (I)	Controls and Dimming	
Type description	No	Dimmable	Yes
CE mark	CE mark	Mechanical and Housing	
ENEC mark	ENEC mark	Housing Material	Aluminum die-cast
UL mark	-	Optic material	Glass
CQC mark	CQC-mark	Optical cover/lens material	Tempered glass
Lifetime to 70% luminous flux	50000 h	Optical cover/lens shape	Flat
Optic type outdoor	Narrow beam angle 10°		
PSE mark	No		
RoHS mark	-		
WEEE mark	-		

Vaya Flood HP

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]

Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	9700 lm
Init. Corr. Color Temperature	5000 K
Init. Color Rendering Index	80


Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	60000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 70% at 50°C Calculated	58000
Lumen Maintenance 70% at 50°C Reported	58000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	37000
Lumen Maintenance 80% at 40°C Reported	37000
Lumen Maintenance 80% at 50°C Reported	36000
Lumen Maintenance 90% at 25°C Calculated	23000

Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	18000
Lumen Maintenance 90% at 40°C Reported	18000
Lumen Maintenance 90% at 50°C Reported	18000

Application Conditions	
Ambient temperature range	-40 to +104 °F

Product Data	
Full product code	871829163550599
Order product name	BCP418 48xLED-HB/5000 220-240V 10 CE CQC
EAN/UPC - Product	8718291635505
Order code	912400130405
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400130405
Net Weight (Piece)	7.600 kg

Dimensional drawing



Vaya

