



Vaya Flood HP

BCP418 48xLED-HB/5000 220-240V 20 CE CQC

48 pcs - LED High Brightness - Medium beam angle 20°

Vaya Flood HP is a reliable and cost-effective white/color-changing floodlight, designed for large-scale exterior installations. The light levels achieved by this compact fixture make it ideal for extensive wall-washing and floodlighting applications – in both static or dynamic colors. Integrated power and DMX512 control make this product easy to use with Philips or third-party DMX controllers.

Product data

General Information			
Number of light sources	48 [48 pcs]	Angle	20°
Lamp family code	LED-HB [LED High Brightness]	Light Technical	
Lamp colour code	Cool white	Standard tilt angle post-top	0°
Light source replaceable	No	Standard tilt angle side entry	0°
Driver included	Yes	Operating and Electrical	
Optical cover/lens type	FG [Flat glass]	Input voltage	220 to 240 V
Luminaire light beam spread	20°	Input frequency	50 to 60 Hz
Protection class IEC	Safety class I (I)	Controls and Dimming	
Type description	No	Dimmable	Yes
CE mark	CE mark	Mechanical and Housing	
ENEC mark	ENEC mark	Housing material	Aluminum die-cast
UL mark	No	Optic material	Glass
CQC mark	CQC-mark	Optical cover/lens material	Tempered glass
Lifetime to 70% luminous flux	50000 h	Optical cover/lens shape	Flat
Outdoor optic type	Medium beam angle 20°	Colour	Dark Grey
PSE mark	No		
RoHS mark	-		
WEEE mark	-		

Vaya Flood HP


Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Initial Performance (IEC Compliant)	
Initial luminous flux	9700 lm
Lamp colour temperature	5000 K
Colour Rendering Index	80
Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	60000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 70% at 50°C Calculated	58000
Lumen Maintenance 70% at 50°C Reported	58000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	37000
Lumen Maintenance 80% at 40°C Reported	37000
Lumen Maintenance 80% at 50°C Reported	36000

Lumen Maintenance 90% at 25°C Calculated	23000
Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	18000
Lumen Maintenance 90% at 40°C Reported	18000
Lumen Maintenance 90% at 50°C Reported	18000

Application Conditions	
Ambient temperature range	-40 to +40 °C

Product Data	
Full product code	871829163551299
Order product name	BCP418 48xLED-HB/5000 220-240V 20 CE CQC
EAN/UPC – product	8718291635512
Order code	912400130406
Numerator – quantity per pack	1
Numerator – packs per outer box	2
Material no. (12NC)	912400130406
Net weight (piece)	7.600 kg

Dimensional drawing



Vaya

