



eW Flex Micro

eW Flex Micro, 3000 K, Clear Dome Lens, Black Housing, 12 in On-Center Node Spacing

eW Flex Micro, 3000 K, Clear Dome Lens, Black Housing, 12 in On-Center Node Spacing

eW Flex Micro is a versatile strand of small, individually controllable white- light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Micro can also be used to light tight alcove spaces and signage.

Product data

General information	
Number of light sources	50 [50 pcs]
Lamp family code	LED-MD [LED Multi-die]
Light source colour	Warm white
Light source replaceable	No
Driver included	Yes
Optic type	WB [Wide beam]
Optical cover/lens type	CLDM12 [Clear dome 12 inch separated]
CE mark	CE mark
ENEC mark	-
UL mark	UL and cUL mark
Product recyclability	100%
EU RoHS compliant	No
Operating and electrical	
Input Voltage	24 V

Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing material	Polycarbonate
Optic material	Polycarbonate
Colour	Black
Approval and application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
FCC mark	FCC Class A
Initial performance (IEC compliant)	
Init. Corr. Colour Temperature	3000 K


eW Flex Micro

Initial input power	25 W
Over time performance (IEC compliant)	
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	60000
Lumen Maintenance 80% at 25 °C Calculated	90000
Lumen Maintenance 80% at 25 °C Reported	60000
Lumen Maintenance 80% at 50 °C Calculated	61000
Lumen Maintenance 80% at 50 °C Reported	60000
Lumen Maintenance 90% at 25 °C Calculated	38000
Lumen Maintenance 90% at 25 °C Reported	38000
Lumen Maintenance 90% at 50 °C Calculated	27000
Lumen Maintenance 90% at 50 °C Reported	27000
Application conditions	
Ambient temperature range	-30 to +50 °C


Product data	
Full product code	871829163910799
Order product name	BGC482 50 3000K CLDM12 BK
EAN/UPC – product	8718291639107
Order code	500-000011-13
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	912400130457
Net Weight (Piece)	0.792 kg
Commercial Code	500-000011-13
Catalogue number description	eW Flex Micro, 3000 K, Clear Dome Lens, Black Housing, 12 in On-Center Node Spacing



Dimensional drawing



BGC482 50 3000K CLDM12 BK



BGC482 50 3000K CLDM12 BK

