



eW Flex Micro

BGC482 50 3500K CLDM12 BK

eW Flex Micro, 3500 K, Clear Dome Lens, Black Housing, 12 in On-Center Node Spacing

eW Flex Micro is a versatile strand of small, individually controllable white- light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Micro can also be used to light tight alcove spaces and signage.

Product data

General Information	
Number of light sources	50 [50 pcs]
Lamp family code	LED-MD [LED Multi-die]
Light source colour	Neutral white
Light source replaceable	No
Driver included	Yes
Optic type	WB [Wide beam]
Optical cover/lens type	CLDM12 [Clear dome 12 inch separated]
CE mark	CE mark
ENEC mark	-
UL mark	UL and cUL mark
Product recyclability	100%
EU RoHS compliant	No
Operating and Electrical	
Input Voltage	24 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Polycarbonate
Optic material	Polycarbonate
Colour	Black
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Initial Performance (IEC Compliant)	
Init. Corr. Colour Temperature	3500 K
Initial input power	25 W

eW Flex Micro

Over Time Performance (IEC Compliant)

Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	60000
Lumen Maintenance 80% at 25 °C Calculated	90000
Lumen Maintenance 80% at 25 °C Reported	60000
Lumen Maintenance 80% at 50 °C Calculated	61000
Lumen Maintenance 80% at 50 °C Reported	60000
Lumen Maintenance 90% at 25 °C Calculated	38000
Lumen Maintenance 90% at 25 °C Reported	38000
Lumen Maintenance 90% at 50 °C Calculated	27000
Lumen Maintenance 90% at 50 °C Reported	27000

Application Conditions


Ambient temperature range	-30 to +50 °C
---------------------------	---------------

Product Data


Full product code	871829163918399
Order product name	BGC482 50 3500K CLDM12 BK
EAN/UPC – product	8718291639183
Order code	500-000011-21
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	912400130465
SAP net weight (piece)	1.008 kg
Commercial Code	500-000011-21
Catalogue number description	eW Flex Micro, 3500 K, Clear Dome Lens, Black Housing, 12 in On-Center Node Spacing



Dimensional drawing



BGC482 50 3500K CLDM12 BK



BGC482 50 3500K CLDM12 BK

