



# eW Flex Compact

## eW Flex Compact, 2700 K, Translucent Dome Lens, White Housing, 4 in on-center node spacing

eW Flex Compact, 2700 K, Translucent Dome Lens, White Housing, 4 in on-center node spacing

eW Flex Compact is a versatile strand of large, individually controllable white-light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Compact can also be used to light tight alcove spaces and signage.

### Product data

General information	
Number of light sources	50 [ 50 pcs]
Lamp family code	LED-MD [ LED Multi-die]
Light source replaceable	No
Driver included	No
Optical cover/lens type	TSDM4 [ Transparent dome 4 inch separated]
CE mark	CE mark
ENEC mark	-
UL mark	UL mark
Product recyclability	100%
EU RoHS compliant	No
Light technical	
Luminance per node	10660 cd/m <sup>2</sup>
Luminous intensity (peak value) on beam axis per node	7 cd
Operating and electrical	
Input Voltage	24 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing material	Polycarbonate
Optic material	Polycarbonate
Colour	White
Approval and application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]

## eW Flex Compact

Mech. impact protection code	IK10 [ 20 J vandal-resistant]
FCC mark	FCC Class A

### Initial performance (IEC compliant)

Init. Corr. Colour Temperature	2700 K
Initial input power	50 W

### Over time performance (IEC compliant)

Lumen Maintenance 70% at 25 °C Calculated	56000
Lumen Maintenance 70% at 25 °C Reported	56000
Lumen Maintenance 70% at 50 °C Calculated	56000
Lumen Maintenance 70% at 50 °C Reported	56000
Lumen Maintenance 80% at 25 °C Calculated	37000
Lumen Maintenance 80% at 25 °C Reported	37000
Lumen Maintenance 80% at 50 °C Calculated	37000
Lumen Maintenance 80% at 50 °C Reported	37000
Lumen Maintenance 90% at 25 °C Calculated	20000
Lumen Maintenance 90% at 25 °C Reported	20000
Lumen Maintenance 90% at 50 °C Calculated	20000
Lumen Maintenance 90% at 50 °C Reported	20000

### Application conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Product data

Full product code	871829164579599
Order product name	BGC481 50 2700K TSDM4 WH
EAN/UPC – product	8718291645795
Order code	500-000012-02
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400130621
Net Weight (Piece)	0.980 kg
Commercial Code	500-000012-02
Catalogue number description	eW Flex Compact, 2700 K, Translucent Dome Lens, White Housing, 4 in-center node spacing

