



# eW Flex Compact

## eW Flex Compact, 5700 K, Clear Flat Lens, White Housing, 4 in On-Center Node Spacing

eW Flex Compact, 5700 K, Clear Flat Lens, White Housing, 4 in On-Center Node Spacing

eW Flex Compact is a versatile strand of large, individually controllable white-light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Compact can also be used to light tight alcove spaces and signage.

### Product data

General Information	
Number of light sources	50 [ 50 pcs]
Lamp family code	LED-MD [ LED Multi-die]
Light source replaceable	No
Driver included	No
Optical cover/lens type	CLFT4 [ Clear flat 4 inch separated]
CE mark	CE mark
ENEC mark	-
UL mark	UL mark
Product recyclability	100%
EU RoHS compliant	No
Operating and Electrical	
Input Voltage	24 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Polycarbonate
Optic material	Polycarbonate
Colour	White
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Initial Performance (IEC Compliant)	
Init. Corr. Colour Temperature	5700 K
Initial input power	1 W

# eW Flex Compact

## Over Time Performance (IEC Compliant)

Lumen Maintenance 70% at 25 °C Calculated	56000
Lumen Maintenance 70% at 25 °C Reported	56000
Lumen Maintenance 70% at 50 °C Calculated	56000
Lumen Maintenance 70% at 50 °C Reported	56000
Lumen Maintenance 80% at 25 °C Calculated	37000
Lumen Maintenance 80% at 25 °C Reported	37000
Lumen Maintenance 80% at 50 °C Calculated	37000
Lumen Maintenance 80% at 50 °C Reported	37000
Lumen Maintenance 90% at 25 °C Calculated	20000
Lumen Maintenance 90% at 25 °C Reported	20000
Lumen Maintenance 90% at 50 °C Calculated	20000
Lumen Maintenance 90% at 50 °C Reported	20000

## Application Conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Product Data

Full product code	871829164609999
Order product name	BGC481 50 5700K CLFT4 WH
EAN/UPC – product	8718291646099
Order code	500-000012-32
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400130651
SAP net weight (piece)	0.980 kg
Commercial Code	500-000012-32
Catalogue number description	eW Flex Compact, 5700 K, Clear Flat Lens, White Housing, 4 in On-Center Node Spacing



## Dimensional drawing



eW Flex SLX

