



# eW Flex Compact

## eW Flex Compact, 6500 K, Clear Flat Lens, Black Housing, 4 in On-Center Node Spacing

eW Flex Compact, 6500 K, Clear Flat Lens, Black Housing, 4 in On-Center Node Spacing

eW Flex Compact is a versatile strand of 50 individually controllable LED nodes. The flexible form factor allows dynamic points of white light to be installed across nearly any interior or exterior surface, including walls, ceilings, floors, three-dimensional sculptures and set pieces. eW Flex Compact can also light tight alcove spaces and signage, and in certain cases, can even display video.

### Product data

General Information		Controls and Dimming	
Number of light sources	50 [ 50 pcs]	Dimmable	Yes
Lamp family code	LED-MD [ LED Multi-die]		
Light source replaceable	No	Mechanical and Housing	
Driver included	No	Housing material	Polycarbonate
Optical cover/lens type	CLFT4 [ Clear flat 4 inch separated]	Optic material	Polycarbonate
CE mark	CE mark	Colour	Black
ENEC mark	-		
UL mark	UL mark	Approval and Application	
Product recyclability	100%	Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
EU RoHS compliant	No	Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Operating and Electrical		Initial Performance (IEC Compliant)	
Input Voltage	24 V	Lamp colour temperature	6500 K
		Initial input power	1 W

eW Flex Compact


Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25 °C Calculated	56000
Lumen Maintenance 70% at 25 °C Reported	56000
Lumen Maintenance 70% at 50 °C Calculated	56000
Lumen Maintenance 70% at 50 °C Reported	56000
Lumen Maintenance 80% at 25 °C Calculated	37000
Lumen Maintenance 80% at 25 °C Reported	37000
Lumen Maintenance 80% at 50 °C Calculated	37000
Lumen Maintenance 80% at 50 °C Reported	37000
Lumen Maintenance 90% at 25 °C Calculated	20000
Lumen Maintenance 90% at 25 °C Reported	20000
Lumen Maintenance 90% at 50 °C Calculated	20000
Lumen Maintenance 90% at 50 °C Reported	20000

Application Conditions	
Ambient temperature range	-40 to +50 °C

Product Data	
Full product code	871829164618199
Order product name	BGC481 50 6500K CLFT4 BK
EAN/UPC – product	8718291646181
Order code	500-000012-41
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400130660
SAP net weight (piece)	0.980 kg
Commercial Code	500-000012-41
Commercial Code	eW Flex Compact, 6500 K, Clear Flat Lens, Black Housing, 4 in On-Center Node Spacing



Dimensional drawing



eW Flex SLX

