



PureStyle IntelliHue Powercore



PureStyle IntelliHue Powercore, 30° x 60°, 305 mm (12 in), Medium Beam Angle

PureStyle IntelliHue Powercore, 30° x 60°, 305 mm (12 in), Medium Beam Angle

Innovative PureStyle Powercore luminaires bring lighting professionals high output in a compact, easily concealed luminaire. PureStyle delivers exceptionally high-quality light for a wide range of interior applications – from cove to wall-washing to backlighting and beyond. Here are just some of the powerful advantages that PureStyle brings to lighting professionals and their clients.

Product data

General information		CRI @ 2,700	
Light source colour	IntelliHue		92.7
Optic type	MB [Medium beam]	Operating and electrical	
Optical cover/lens type	PC [Polycarbonate bowl/cover]	Input Voltage	100 to 277 V
Luminaire light beam spread	30° x 60°	Mechanical and housing	
CE mark	CE mark	Housing material	Extruded aluminium
UL mark	UL and cUL mark	Length	305 mm
Light technical		Colour	White
Efficacy (lm/W) @ 4,000 K	61 lm/W	Approval and application	
Efficacy (lm/W) @ 2,700 K	61 lm/W	Ingress protection code	IP20 [Finger-protected]
CRI @ 4,000 K	90.7	Energy Efficiency Class	G
CRI R9 @ 4,000 K	57.8	FCC mark	FCC Class B


PureStyle IntelliHue Powercore

	887770
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	696 lm
Initial LED luminaire efficacy at RGB operation	61 lm/W
Initial input power	13 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Calculated	72300
Lumen Maintenance 50% at 25 °C Reported	47100
Lumen Maintenance 50% at 50 °C Calculated	72300
Lumen Maintenance 50% at 50 °C Reported	47100
Application conditions	
Ambient temperature range	-20 to +50 °C

Product data

Full product code	871829139149499
Order product name	SA500X 30X60 INTELLIHUE L305
EAN/UPC – product	8718291391494
Order code	123-000025-01
SAP numerator – quantity per pack	1
Numerator – packs per outer box	20
SAP material	912400133449
Net Weight (Piece)	0.485 kg
Commercial Code	123-000025-01
Catalogue number description	PureStyle IntelliHue Powercore, 30° x 60°, 305 mm (12 in), Medium Beam Angle

Dimensional drawing



SA500X 30X60 INTELLIHUE L305

