



PureStyle IntelliHue Powercore



PureStyle IntelliHue Powercore, 30° x 60°, 1219 mm (48 in), Medium Beam Angle

PureStyle IntelliHue Powercore, 30° x 60°, 1219 mm (48 in), Medium Beam Angle

Innovative PureStyle Powercore luminaires bring lighting professionals high output in a compact, easily concealed luminaire. PureStyle delivers exceptionally high-quality light for a wide range of interior applications from cove to wall-washing to backlighting and beyond. Here are just some of the powerful advantages that PureStyle brings to lighting professionals and their clients.

Product data


General information		CRI @ 2700	
Light source color	IntelliHue	92.7	
Optic type	Medium beam		
Optical cover/lens type	Polycarbonate bowl/cover	Operating and electrical	
Luminaire light beam spread	30° x 60°	Input Voltage	100 to 277 V
CE mark	CE mark	Mechanical and housing	
UL mark	UL and cUL mark	Housing Material	Aluminum extruded
Light technical		Length	1220 mm
Efficacy (lm/W) @ 4000 K	61 lm/W	Color	White
Efficacy (lm/W) @ 2700 K	61 lm/W	Approval and application	
CRI @ 4000 K	90.7	Ingress protection code	IP20 [Finger-protected]
CRI R9 @ 4000 K	57.8	Energy Efficiency Class	G
		FCC mark	FCC Class B

PureStyle IntelliHue Powercore

EPREL Registration Number	887773
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	2784 lm
Initial LED luminaire efficacy at RGB operation	61 lm/W
Initial input power	52 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25°C Calculated	72300
Lumen Maintenance 50% at 25°C Reported	47100
Lumen Maintenance 50% at 50°C Calculated	72300
Lumen Maintenance 50% at 50°C Reported	47100
Application conditions	
Ambient temperature range	-20 to +50 °C

Product data	
Full product code	871829139152499
Order product name	SA500X 30X60 INTELLIHUE L1220
EAN/UPC - Product	8718291391524
Order code	123-000025-04
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912400133452
Net Weight (Piece)	1.847 kg
Catalog Number	123-000025-04
Catalog Number Description	PureStyle IntelliHue Powercore, 30° x 60°, 1219 mm (48 in), Medium Beam Angle

Dimensional drawing



SA500X 30X60 INTELLIHUE L1220

