



PureStyle Intelligent Color Powercore, RGBA



PureStyle Intelligent Color Powercore, RGBA, 100° x 100°, 305 mm (12 in), Wide Beam Angle

PureStyle Intelligent Color Powercore, RGBA, 100° x 100°, 305 mm (12 in), Wide Beam Angle

Innovative PureStyle Powercore luminaires bring lighting professionals high output in a compact, easily concealed luminaire. PureStyle delivers exceptionally high-quality light for a wide range of interior applications from cove to wall-washing to backlighting and beyond. Here are just some of the powerful advantages that PureStyle brings to lighting professionals and their clients.

Product data


General information		Mechanical and housing	
Light source color	RGBA	Housing Material	Aluminum extruded
Optic type	Wide beam	Length	305 mm
Optical cover/lens type	Polycarbonate bowl/cover	Color	White
Luminaire light beam spread	100° x 100°	Approval and application	
CE mark	CE mark	Ingress protection code	IP20 [Finger-protected]
UL mark	UL and cUL mark	Energy Efficiency Class	G
Operating and electrical		FCC mark	FCC Class B
Input Voltage	100 to 277 V	EPREL Registration Number	887775

PureStyle Intelligent Color Powercore, RGBA

Initial performance (IEC compliant)	
Initial luminous flux (system flux)	528 lm
Initial LED luminaire efficacy at RGB operation	41 lm/W
Initial input power	13 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25°C Calculated	72300
Lumen Maintenance 50% at 25°C Reported	47100
Lumen Maintenance 50% at 50°C Calculated	72300
Lumen Maintenance 50% at 50°C Reported	47100
Application conditions	
Ambient temperature range	-20 to +50 °C
Product data	
Full product code	871829139154899

Order product name	SA500X 120X120 RGBA L305
EAN/UPC - Product	8718291391548
Order code	123-000026-00
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	912400133454
Net Weight (Piece)	0.485 kg
Catalog Number	123-000026-00
Catalog Number Description	PureStyle Intelligent Color Powercore, RGBA, 100° x 100°, 305 mm (12 in), Wide Beam Angle

Dimensional drawing



SA500X 120X120 RGBA L305

