



# PureStyle Intelligent Colour RGBA Powercore

## PureStyle Intelligent Color Powercore, RGBA, 10° x 60°, 305 mm (12 in), Narrow Beam Angle

PureStyle Intelligent Color Powercore, RGBA, 10° x 60°, 305 mm (12 in), Narrow Beam Angle

Innovative PureStyle Powercore luminaires bring lighting professionals high output in a compact, easily concealed luminaire. PureStyle delivers exceptionally high-quality light for a wide range of interior applications, from cove to wall-washing to backlighting and beyond. Here are just some of the powerful advantages that PureStyle brings to lighting professionals and their clients.


### Product data

General information		Mechanical and housing	
Lamp colour code	RGBA	Housing material	Aluminum extruded
Optic type	NB [ Narrow beam]	Length	305 mm
Optical cover/lens type	PC [ Polycarbonate bowl/cover]	Colour	White
Luminaire light beam spread	10° x 60°	Approval and application	
CE mark	CE mark	Ingress protection code	IP20 [ Finger-protected]
UL mark	UL and cUL mark	Energy Efficiency Class	G
Operating and electrical		FCC mark	FCC Class B
Input Voltage	100 to 277 V		887777

# PureStyle Intelligent Colour RGBA Powercore

Initial performance (IEC compliant)		Product data	
Initial luminous flux (system flux)	549 lm	Full product code	871829139156299
Initial LED luminaire efficacy at RGB operation	42 lm/W	Order product name	SA500X 10X60 RGBA L305
Initial input power	13 W	EAN/UPC – product	8718291391562
		Order code	123-000026-02
		SAP numerator – quantity per pack	1
		Numerator – packs per outer box	20
		SAP material	912400133456
		Net Weight (Piece)	0.485 kg
		Commercial Code	123-000026-02
		Commercial Code	PureStyle Intelligent Color Powercore, RGBA, 10° x 60°, 305 mm (12 in), Narrow Beam Angle
Over time performance (IEC compliant)			
Lumen Maintenance 50% at 25 °C Calculated	72300		
Lumen Maintenance 50% at 25 °C Reported	47100		
Lumen Maintenance 50% at 50 °C Calculated	72300		
Lumen Maintenance 50% at 50 °C Reported	47100		
Application conditions			
Ambient temperature range	-20 to +50 °C		

## Dimensional drawing



SA500X 10X60 RGBA L305

