



eW Reach Compact Powercore

DCP400 3000 CO 100-277V UL CE

3000 K - 5° - 100 to 277 V - Flat glass

eW Reach Compact Powercore high-performance LED luminaires are premium exterior long-throw dynamic high-quality white luminaires for lighting tall buildings, bridges, and iconic structures. eW Reach Compact Powercore outputs washes of white light in color temperatures ranging from a warm 2700 K to a cool 6500 K. A full range of accessories allow for customizable beam angles for floodlighting, spotlighting, wall washing, and grazing, along with the efficiency and cost-effectiveness of Powercore technology in a rugged die-cast aluminium housing.

Product data

General Information		Control signal voltage	
Number of light sources	52 pcs	Control signal voltage	1-10 V DC
Light source replaceable	No	Controls and Dimming	
Optical cover/lens type	Flat glass	Dimmable	Yes
Luminaire light beam spread	5°	Approval and Application	
Protection class IEC	Safety class I	Mech. impact protection code	IK07 [2 J reinforced]
Flammability mark	For mounting on normally flammable surfaces	Initial Performance (IEC Compliant)	
CE mark	CE mark	Luminous flux tolerance	+/-10%
Warranty period	5 years	Init. Corr. Color Temperature	3000 K
RoHS mark	RoHS mark	Init. Color Rendering Index	79
WEEE mark	WEEE mark	Initial input power	125 W
Operating and Electrical		Power consumption tolerance	+/-10%
Input Voltage	100 to 277 V		
Input Frequency	50 to 60 Hz		

eW Reach Compact Powercore


Application Conditions

Ambient temperature range -40 to +50 °C


Product Data

Full product code 871829139015200
Order product name DCP400 3000 CO 100-277V UL CE
EAN/UPC - Product 8718291390152
Order code 912400133471

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400133471
Net Weight (Piece)	23.400 kg



Dimensional drawing



Reach Compact

