



iColor Accent Compact



iColor Accent Compact, RGB, 305 mm (12 in), Translucent Lens

iColor Accent Compact, RGB, 305 mm (12 in), Translucent Lens

iColor Accent Compact is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics, and intricately designed effects in a host of architectural settings. iColor Accent Compact accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

Product data



General information		Corrosion Resistance	
Light source color	RGB	Complies with ASTM B117 standard for > 1,500 hours	
Optical cover/lens type	Polycarbonate bowl/cover transparent	FCC mark	
Light technical		FCC Class A	
On-axis intensity in candela	20	Vibration Rating	
Mechanical and housing		Complies with ANSI C136.31, 3G	
Length	305 mm	EPREL Registration Number	
Color	Aluminum	1081399	
Approval and application		Initial performance (IEC compliant)	
Energy Efficiency Class	G	Initial input power	
Vibration Standard	Complies with ANSI C136.31, 3G	10 W	
		Over time performance (IEC compliant)	
		Lumen Maintenance 50% at 25°C Reported	
		60000	
		Lumen Maintenance 50% at 50°C Reported	
		60000	
		Lumen Maintenance 70% at 25°C Reported	
		60000	

iColor Accent Compact

Lumen Maintenance 70% at 50°C Reported 60000	
Product data	
Full product code	871829139180799
Order product name	BCS425 RGB FR ETH L305 PP19
EAN/UPC - Product	8718291391807
Order code	101-000200-00

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	9
Material Nr. (12NC)	912400133771
Net Weight (Piece)	0.630 kg
Catalog Number	101-000200-00

Dimensional drawing



BCS425 RGB FR ETH L305 PP19

BCS425 RGB FR ETH L305 PP19

