



iColor Accent Compact

iColor Accent Compact, RGB, 1220 mm (48 in), Translucent Lens

iColor Accent Compact, RGB, 1220 mm (48 in), Translucent Lens

iColor Accent Compact is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics and intricately designed effects in a host of architectural settings. iColor Accent Compact accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

Product data


General information		Vibration standard		Complies with ANSI C136.31, 3G
Light source colour	RGB	Vibration rating		Complies with ANSI C136.31, 3G
Optical cover/lens type	PCT [Polycarbonate bowl/cover transparent]			1081401
Light technical		Initial performance (IEC compliant)		
On-axis intensity in candela	80	Initial input power		28 W
Mechanical and housing		Over time performance (IEC compliant)		
Length	1220 mm	Lumen Maintenance 50% at 25 °C Reported		60000
Colour	Aluminum	Lumen Maintenance 50% at 50 °C Reported		60000
Approval and application		Lumen Maintenance 70% at 25 °C Reported		60000
Energy Efficiency Class	G	Lumen Maintenance 70% at 50 °C Reported		60000

iColor Accent Compact


Product data	
Full product code	871829139182199
Order product name	BCS425 RGB FR ETH L1220 PP19
EAN/UPC – product	8718291391821
Order code	101-000200-02
SAP numerator – quantity per pack	1

Numerator – packs per outer box	9
SAP material	912400133773
Net Weight (Piece)	1.640 kg
Commercial Code	101-000200-02

Dimensional drawing



BCS425 RGB FR ETH L1220 PP19



BCS425 RGB FR ETH L1220 PP19

