



# iColor Accent Compact



## iColor Accent Compact, RGB, 1220 mm (48 in), Translucent Lens

iColor Accent Compact, RGB, 1220 mm (48 in), Translucent Lens

iColor Accent Compact is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics and intricately designed effects in a host of architectural settings. iColor Accent Compact accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

### Product data

General information		Vibration standard	
Light source colour	RGB	Vibration standard	Complies with ANSI C136.31, 3G
Optical cover/lens type	PCT [ Polycarbonate bowl/cover transparent]	Vibration rating	Complies with ANSI C136.31, 3G
			1081401
Light technical		Initial performance (IEC compliant)	
On-axis intensity in candela	80	Initial input power	28 W
Mechanical and housing		Over time performance (IEC compliant)	
Length	1220 mm	Lumen Maintenance 50% at 25 °C Reported	60000
Colour	Aluminium	Lumen Maintenance 50% at 50 °C Reported	60000
		Lumen Maintenance 70% at 25 °C Reported	60000
		Lumen Maintenance 70% at 50 °C Reported	60000
Approval and application			
Energy Efficiency Class	G		


# iColor Accent Compact

## Product data


Full product code	871829139182199
Order product name	BCS425 RGB FR ETH L1220 PP19
EAN/UPC – product	8718291391821
Order code	101-000200-02
SAP numerator – quantity per pack	1

Numerator – packs per outer box	9
SAP material	912400133773
Net Weight (Piece)	1.640 kg
Commercial Code	101-000200-02

## Dimensional drawing



BCS425 RGB FR ETH L1220 PP19



BCS425 RGB FR ETH L1220 PP19

