



iColor Accent Compact



iColor Accent Compact, RGB, 305 mm (12 in), Clear Lens

iColor Accent Compact, RGB, 305 mm (12 in), Clear Lens

iColor Accent Compact is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics, and intricately designed effects in a host of architectural settings. iColor Accent Compact accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

Product data

General information		Vibration Standard	
Light source color	RGB	Vibration Standard	Complies with ANSI C136.31, 3G
Optical cover/lens type	Polycarbonate bowl/cover UV-resistant	Corrosion Resistance	Complies with ASTM B117 standard for > 1,500 hours
Luminaire light beam spread	105°	FCC mark	FCC Class A
Light technical		Vibration Rating	Complies with ANSI C136.31, 3G
On-axis intensity in candela	47	EPREL Registration Number	1081402
Mechanical and housing		Initial performance (IEC compliant)	
Length	305 mm	Initial input power	10 W
Color	Aluminum	Over time performance (IEC compliant)	
Approval and application		Lumen Maintenance 50% at 25°C Reported	60000
Energy Efficiency Class	G	Lumen Maintenance 50% at 50°C Reported	60000
		Lumen Maintenance 70% at 25°C Reported	60000

iColor Accent Compact



Lumen Maintenance 70% at 50°C Reported 60000

Product data

Full product code	871829139183899
Order product name	BCS425 RGB CL ETH L305 PP19
EAN/UPC - Product	8718291391838
Order code	101-000200-03

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	9
Material Nr. (12NC)	912400133774
Net Weight (Piece)	0.610 kg
Catalog Number	101-000200-03

Dimensional drawing



BCS425 RGB CL ETH L305 PP19

BCS425 RGB CL ETH L305 PP19

