



# iColor Accent Compact



## iColor Accent Compact, RGB, 609 mm (24 in), Clear Lens

iColor Accent Compact, RGB, 609 mm (24 in), Clear Lens

iColor Accent Compact is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics and intricately designed effects in a host of architectural settings. iColor Accent Compact accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

### Product data


General information		Approval and application	
Light source colour	RGB	Energy Efficiency Class	G
Optical cover/lens type	PC-UV [ Polycarbonate bowl/cover UV-resistant]	Vibration standard	Complies with ANSI C136.31, 3G
Luminaire light beam spread	105°	Vibration rating	Complies with ANSI C136.31, 3G 1081403
Light technical		Initial performance (IEC compliant)	
On-axis intensity in candela	94	Initial input power	16 W
Mechanical and housing		Over time performance (IEC compliant)	
Length	610 mm	Lumen Maintenance 50% at 25 °C Reported	60000
Colour	Aluminium	Lumen Maintenance 50% at 50 °C Reported	60000
		Lumen Maintenance 70% at 25 °C Reported	60000

iColor Accent Compact


Lumen Maintenance 70% at 50 °C Reported 60000	
Product data	
Full product code	871829139184599
Order product name	BCS425 RGB CL ETH L610 PP19
EAN/UPC – product	8718291391845
Order code	101-000200-04
SAP numerator – quantity per pack	1

Numerator – packs per outer box	9
SAP material	912400133775
Net Weight (Piece)	0.910 kg
Commercial Code	101-000200-04
Catalogue number description	iColor Accent Compact, RGB, 609 mm (24 in), Clear Lens

Dimensional drawing



BCS425 RGB CL ETH L610 PP19



BCS425 RGB CL ETH L610 PP19

