



iColor Accent Compact

iColor Accent Compact, RGB, 1220 mm (48 in), Translucent Lens

iColor Accent Compact, RGB, 1220 mm (48 in), Translucent Lens

iColor Accent Compact is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics and intricately designed effects in a host of architectural settings. iColor Accent Compact accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

Product data

General information	
Light source colour	RGB
Optical cover/lens type	PC-UV [Polycarbonate bowl/cover UV-resistant]
Luminaire light beam spread	105°
Light technical	
On-axis intensity in candela	188
Mechanical and housing	
Length	1220 mm
Colour	Aluminum


Approval and application	
Energy Efficiency Class	G
Vibration standard	Complies with ANSI C136.31, 3G
Vibration rating	Complies with ANSI C136.31, 3G 1081404
Initial performance (IEC compliant)	
Initial input power	28 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 50 °C Reported	60000
Lumen Maintenance 70% at 25 °C Reported	60000

iColor Accent Compact


Lumen Maintenance 70% at 50 °C Reported 60000	
Product data	
Full product code	871829139185299
Order product name	BCS425 RGB CL ETH L1220 PP19
EAN/UPC – product	8718291391852
Order code	101-000200-05

SAP numerator – quantity per pack	1
Numerator – packs per outer box	9
SAP material	912400133776
Net Weight (Piece)	1.530 kg
Commercial Code	101-000200-05

Dimensional drawing



BCS425 RGB CL ETH L1220 PP19



BCS425 RGB CL ETH L1220 PP19

