



# Vaya Flood LP Small



## BCP431 RGB 100-240 10 CE CQC PSE

Vaya Flood LP G2, RGB, 10°, CE/CQC/PSE

With budgets under pressure, property owners and developers are looking, more than ever, for value for money when it comes to capital expenditures. Vaya Flood is an affordable and reliable LED solution that minimizes the initial investment, while providing exceptional flexibility to create eye-catching, dynamic and colourful lighting effects that can bring a property to life. The robust Vaya Flood offers a wide choice of mono colours with a simple on-off switch and changing colours with a standard DMX512 controller. It is also extremely easy to install and aim.

### Product data

General Information	
Lamp family code	LED-HB [ LED High Brightness]
Lamp colour code	Red, green and blue
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	GT [ Tempered glass]
Protection class IEC	Safety class I (I)
CE mark	CE mark
CQC mark	CQC-mark
Optic type outdoor	Narrow beam angle 10°
PSE mark	PSE mark
Angle	10°
Operating and Electrical	
Input Voltage	100 to 240 V
Input frequency	50 to 60 Hz

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Aluminum die-cast
Optic material	Glass
Optical cover/lens material	Tempered glass
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Colour	Dark Grey
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK06 [ 1 J]
Vibration standard	Complies with ANSI C136.31
Vibration rating	Complies with ANSI C136.31

## Vaya Flood LP Small


915382	
<b>Initial Performance (IEC Compliant)</b>	
Initial luminous flux (system flux)	1542 lm
Initial LED luminaire efficacy	38.4 lm/W
Initial input power	45 W
<b>Over Time Performance (IEC Compliant)</b>	
Lumen Maintenance 50% at 25 °C Calculated	100000
Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 40 °C Calculated	100000
Lumen Maintenance 50% at 40 °C Reported	60000
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 40 °C Calculated	100000
Lumen Maintenance 70% at 40 °C Reported	60000

### Application Conditions


Ambient temperature range	-40 to +40 °C
---------------------------	---------------

### Product Data

Full product code	871829164706599
Order product name	BCP431 RGB 100-240 10 CE CQC PSE
EAN/UPC – product	8718291647065
Order code	316-000015-00
SAP numerator – quantity per pack	1
Numerator – packs per outer box	4
SAP material	912400133898
SAP net weight (piece)	2.800 kg
Commercial Code	316-000015-00
Commercial Code	Vaya Flood LP G2, RGB, 10°, CE/CQC/PSE



## Dimensional drawing



Vaya

