



Vaya Flood LP

BCP433 GN 100-240 40 CE CQC PSE

Medium beam angle 40°

Vaya Flood LP (gen2) is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

Product data

| General Information | | Controls and Dimming | |
|-----------------------------|-------------------------------|------------------------------|---|
| Lamp family code | LED-HB [LED High Brightness] | Dimmable | Yes |
| Light source color | Green | | |
| Light source replaceable | No | | |
| Driver included | Yes | | |
| Optical cover/lens type | Tempered glass | | |
| Luminaire light beam spread | 40° | | |
| Protection class IEC | Safety class I | | |
| CE mark | CE mark | | |
| CQC mark | CQC-mark | | |
| Optic type outdoor | Medium beam angle 40° | | |
| PSE mark | PSE mark | | |
| Angle | 40° | | |
| Operating and Electrical | | Mechanical and Housing | |
| Input Voltage | 100 to 240 V | Housing Material | Aluminum die cast |
| Input Frequency | 50 to 60 Hz | Optic material | Glass |
| | | Optical cover/lens material | Tempered glass |
| | | Optical cover/lens shape | Flat |
| | | Optical cover/lens finish | Clear |
| | | Color | Dark gray |
| | | Approval and Application | |
| | | Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| | | Mech. impact protection code | IK06 [1 J] |
| | | Application Conditions | |
| | | Ambient temperature range | -40 to +40 °C |

