



# Vaya Flood LP Small

BCP432 4000 100-240 20 UL

Medium beam angle 20°

With budgets under pressure, property owners and developers are looking, more than ever, for value for money when it comes to capital expenditures. Vaya Flood is an affordable and reliable LED solution that minimizes the initial investment, while providing exceptional flexibility to create eye-catching, dynamic and colorful lighting effects that can bring a property to life. The robust Vaya Flood offers a wide choice of mono colors with a simple on-off switch and changing colors with a standard DMX512 controller. It is also extremely easy to install and aim.

## Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [ LED High Brightness]	Dimmable	Yes
Light source color	Neutral white	<b>Mechanical and Housing</b>	
Light source replaceable	No	Housing Material	Aluminum die-cast
Driver included	Yes	Optic material	Glass
Optical cover/lens type	GT [ Tempered glass]	Optical cover/lens material	Tempered glass
Luminaire light beam spread	20°	Optical cover/lens shape	Flat
Protection class IEC	Safety class I (I)	Optical cover/lens finish	Clear
UL mark	UL and cUL mark	<b>Approval and Application</b>	
Optic type outdoor	Medium beam angle 20°	Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
PSE mark	No	Mech. impact protection code	IK06 [ 1 J]
FCC mark	FCC Class A	<b>Initial Performance (IEC Compliant)</b>	
Angle	20°	Initial luminous flux (system flux)	3688 lm
<b>Operating and Electrical</b>		Initial luminous flux at color temperature of 4000 K	3688 lm
Input Voltage	100 to 240 V	Initial LED luminaire efficacy	87.9 lm/W
Input Frequency	50 to 60 Hz		

## Vaya Flood LP Small

Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	82

### Over Time Performance (IEC Compliant)

Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	23000
Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

### Application Conditions


Ambient temperature range	-40 to +104 °F
---------------------------	----------------

### Product Data

Full product code	871829164746199
Order product name	BCP432 4000 100-240 20 UL
EAN/UPC - Product	8718291647461
Order code	912400133935
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400133935
Net Weight (Piece)	2.770 kg

IK06

### Dimensional drawing



Vaya

