



Vaya Flood LP Small

BCP432 4000 100-240 40 UL HMA

Housing with medium-length arm - Medium beam angle 40°

With budgets under pressure, property owners and developers are looking, more than ever, for value for money when it comes to capital expenditures. Vaya Flood is an affordable and reliable LED solution that minimizes the initial investment, while providing exceptional flexibility to create eye-catching, dynamic and colorful lighting effects that can bring a property to life. The robust Vaya Flood offers a wide choice of mono colors with a simple on-off switch and changing colors with a standard DMX512 controller. It is also extremely easy to install and aim.

Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Light source color	Neutral white		
Light source replaceable	No		
Driver included	Yes		
Optical cover/lens type	GT [Tempered glass]		
Luminaire light beam spread	40°		
Protection class IEC	Safety class I (I)		
UL mark	UL and cUL mark		
Optic type outdoor	Medium beam angle 40°		
PSE mark	No		
FCC mark	FCC Class A		
Angle	40°		
Operating and Electrical		Mechanical and Housing	
Input Voltage	100 to 240 V	Housing configuration	HMA [Housing with medium-length arm]
Input Frequency	50 to 60 Hz	Housing Material	Aluminum die-cast
		Optic material	Glass
		Optical cover/lens material	Tempered glass
		Optical cover/lens shape	Flat
		Optical cover/lens finish	Clear
		Approval and Application	
		Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
		Mech. impact protection code	IK06 [1 J]
		Initial Performance (IEC Compliant)	
		Initial luminous flux (system flux)	3387 lm
		Initial luminous flux at color temperature of 4000 K	3387 lm

Vaya Flood LP Small

Initial LED luminaire efficacy	85.7 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	82

Over Time Performance (IEC Compliant)


Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	23000
Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

Application Conditions	
Ambient temperature range	-40 to +40 °C

Product Data	
Full product code	871829164765299
Order product name	BCP432 4000 100-240 40 UL HMA
EAN/UPC - Product	8718291647652
Order code	912400133939
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400133939
Net Weight (Piece)	2.500 kg



Dimensional drawing



Vaya

