



Vaya Flood LP Small

BCP432 2700 100-240 40 CE CQC PSE

Medium beam angle 40°

With budgets under pressure, property owners and developers are looking, more than ever, for value for money when it comes to capital expenditures. Vaya Flood is an affordable and reliable LED solution that minimizes the initial investment, while providing exceptional flexibility to create eye-catching, dynamic and colorful lighting effects that can bring a property to life. The robust Vaya Flood offers a wide choice of mono colors with a simple on-off switch and changing colors with a standard DMX512 controller. It is also extremely easy to install and aim.

Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Light source color	Cool white	Mechanical and Housing	
Light source replaceable	No	Housing Material	Aluminum die-cast
Driver included	Yes	Optic material	Glass
Optical cover/lens type	GT [Tempered glass]	Optical cover/lens material	Tempered glass
Protection class IEC	Safety class I (I)	Optical cover/lens shape	Flat
CE mark	CE mark	Optical cover/lens finish	Clear
CQC mark	CQC-mark	Approval and Application	
Optic type outdoor	Medium beam angle 40°	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
PSE mark	PSE mark	Mech. impact protection code	IK06 [1 J]
Angle	40°	Initial Performance (IEC Compliant)	
Operating and Electrical		Init. Corr. Color Temperature	2700 K
Input Voltage	100 to 240 V		
Input Frequency	50 to 60 Hz		

Vaya Flood LP Small

Over Time Performance (IEC Compliant)

Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	23000
Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

Application Conditions


Ambient temperature range	-40 to +104 °F
---------------------------	----------------

Product Data

Full product code	871829164750899
Order product name	BCP432 2700 100-240 40 CE CQC PSE
EAN/UPC - Product	8718291647508
Order code	912400133942
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400133942
Net Weight (Piece)	2.770 kg



Dimensional drawing



Vaya

