



Vaya Flood LP

BCP432 5000 100-240 10 CE CQC PSE

Narrow beam angle 10°

With budgets under pressure, property owners and developers are looking, more than ever, for value for money when it comes to capital expenditures. Vaya Flood is an affordable and reliable LED solution that minimizes the initial investment, while providing exceptional flexibility to create eye-catching, dynamic and colourful lighting effects that can bring a property to life. The robust Vaya Flood offers a wide choice of mono colours with a simple on-off switch and changing colours with a standard DMX512 controller. It is also extremely easy to install and aim.

Product data

| General Information | |
|-----------------------------|-------------------------------|
| Lamp family code | LED-HB [LED High Brightness] |
| Lamp colour code | Cool white |
| Light source replaceable | No |
| Driver included | Yes |
| Optical cover/lens type | GT [Tempered glass] |
| Luminaire light beam spread | 10° |
| Protection class IEC | Safety class I (I) |
| CE mark | CE mark |
| CQC mark | CQC-mark |
| Outdoor optic type | Narrow beam angle 10° |
| PSE mark | PSE mark |
| Angle | 10° |
| Operating and Electrical | |
| Input voltage | 100 to 240 V |
| Input frequency | 50 to 60 Hz |

| Controls and Dimming | |
|------------------------------|---|
| Dimmable | Yes |
| Mechanical and Housing | |
| Housing material | Aluminum die-cast |
| Optic material | Glass |
| Optical cover/lens material | Tempered glass |
| Optical cover/lens shape | Flat |
| Optical cover/lens finish | Clear |
| Colour | Dark Grey |
| Approval and Application | |
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK06 [1 J] |

Vaya Flood LP

| Initial Performance (IEC Compliant) | |
|--|--------|
| Lamp colour temperature | 5000 K |
| Over Time Performance (IEC Compliant) | |
| Lumen Maintenance 70% at 25°C Calculated | 71000 |
| Lumen Maintenance 70% at 25°C Reported | 60000 |
| Lumen Maintenance 70% at 40°C Calculated | 71000 |
| Lumen Maintenance 70% at 40°C Reported | 60000 |
| Lumen Maintenance 80% at 25°C Calculated | 45000 |
| Lumen Maintenance 80% at 25°C Reported | 45000 |
| Lumen Maintenance 80% at 40°C Calculated | 45000 |
| Lumen Maintenance 80% at 40°C Reported | 45000 |
| Lumen Maintenance 90% at 25°C Calculated | 23000 |
| Lumen Maintenance 90% at 25°C Reported | 23000 |
| Lumen Maintenance 90% at 40°C Calculated | 23000 |
| Lumen Maintenance 90% at 40°C Reported | 23000 |

| Application Conditions | |
|---------------------------------|-----------------------------------|
| Ambient temperature range | -40 to +40 °C |
| Product Data | |
| Full product code | 871829164751599 |
| Order product name | BCP432 5000 100-240 10 CE CQC PSE |
| EAN/UPC – product | 8718291647515 |
| Order code | 912400133945 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 4 |
| Material no. (12NC) | 912400133945 |
| Net weight (piece) | 2.770 kg |



Dimensional drawing



Vaya

