



# Vaya Flood LP

BCP432 5000 100-240 10 CE CQC PSE

Narrow beam angle 10°

Vaya Flood LP (gen2) is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

## Product data

General Information	
Lamp family code	LED-HB [ LED High Brightness]
Light source color	Cool white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	Tempered glass
Luminaire light beam spread	10°
Protection class IEC	Safety class I
CE mark	CE mark
CQC mark	CQC-mark
Optic type outdoor	Narrow beam angle 10°
PSE mark	PSE mark
Angle	10°
Operating and Electrical	
Input Voltage	100 to 240 V
Input Frequency	50 to 60 Hz

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Glass
Optical cover/lens material	Tempered glass
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Color	Dark gray
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [ 1 J]

Vaya Flood LP

Initial Performance (IEC Compliant)	
Init. Corr. Color Temperature	5000 K
Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	23000
Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

Application Conditions	
Ambient temperature range	-40 to +40 °C
Product Data	
Full product code	871829164751599
Order product name	BCP432 5000 100-240 10 CE CQC PSE
EAN/UPC - Product	8718291647515
Order code	912400133945
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400133945
Net Weight (Piece)	2.770 kg



Dimensional drawing



Vaya

