



Vaya Flood LP

BCP432 3000 100-240 40 UL HMA

Housing with medium-length arm - Medium beam angle 40°

Vaya Flood LP (gen2) is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

Product data

General Information	
Lamp family code	LED-HB [LED High Brightness]
Light source color	Neutral white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	Tempered glass
Luminaire light beam spread	40°
Protection class IEC	Safety class I
UL mark	UL and cUL mark
Optic type outdoor	Medium beam angle 40°
PSE mark	No
FCC mark	FCC Class A
Angle	40°
Operating and Electrical	
Input Voltage	100 to 240 V
Input Frequency	50 to 60 Hz

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing configuration	Housing with medium-length arm
Housing Material	Aluminum die cast
Optic material	Glass
Optical cover/lens material	Tempered glass
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Color	Dark gray
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Vibration Standard	Complies with ANSI C136.31


Vaya Flood LP

Vibration Rating	Complies with ANSI C136.31
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	3123 lm
Initial LED luminaire efficacy	73 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	82
Initial input power	44 W
Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	23000

Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000
Application Conditions	
Ambient temperature range	-40 to +40 °C
Product Data	
Full product code	871829164762199
Order product name	BCP432 3000 100-240 40 UL HMA
EAN/UPC - Product	8718291647621
Order code	912400133959
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400133959
Net Weight (Piece)	2.500 kg



Dimensional drawing



Vaya

