



Vaya Flood LP

BCP432 3000 100-240 90 CE CQC PSE

Very wide beam angle 90°

Vaya Flood LP (gen2) is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Light source color	Neutral white		
Light source replaceable	No	Mechanical and Housing	
Driver included	Yes	Housing Material	Aluminum die cast
Optical cover/lens type	Tempered glass	Optic material	Glass
Luminaire light beam spread	90°	Optical cover/lens material	Tempered glass
Protection class IEC	Safety class I	Optical cover/lens shape	Flat
CE mark	CE mark	Optical cover/lens finish	Clear
CQC mark	CQC-mark	Color	Dark gray
Optic type outdoor	Very wide beam angle 90°	Approval and Application	
PSE mark	PSE mark	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Angle	90°	Mech. impact protection code	IK06 [1 J]
Operating and Electrical		Initial Performance (IEC Compliant)	
Input Voltage	100 to 240 V	Init. Corr. Color Temperature	3000 K
Input Frequency	50 to 60 Hz		


Vaya Flood LP

Init. Color Rendering Index	82
Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	71000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	45000
Lumen Maintenance 80% at 25°C Reported	45000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	23000
Lumen Maintenance 90% at 25°C Reported	23000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

Application Conditions	
Ambient temperature range	-40 to +40 °C
Product Data	
Full product code	871829164956499
Order product name	BCP432 3000 100-240 90 CE CQC PSE
EAN/UPC - Product	8718291649564
Order code	912400133960
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400133960
Net Weight (Piece)	2.770 kg



Dimensional drawing



Vaya

