



# Vaya Flood MP Medium

BCP435 3000 120-277 90 UL

Very wide beam angle 90°

With budgets under pressure, property owners and developers are looking, more than ever, for value for money when it comes to capital expenditures. Vaya Flood is an affordable and reliable LED solution that minimizes the initial investment, while providing exceptional flexibility to create eye-catching, dynamic and colorful lighting effects that can bring a property to life. The robust Vaya Flood offers a wide choice of mono colors with a simple on-off switch and changing colors with a standard DMX512 controller. It is also extremely easy to install and aim.

## Product data

General Information	
Lamp family code	LED-HB [ LED High Brightness]
Light source color	Neutral white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	GT [ Tempered glass]
Luminaire light beam spread	90°
Protection class IEC	Safety class I (I)
UL mark	UL and cUL mark
Optic type outdoor	Very wide beam angle 90°
PSE mark	No
FCC mark	FCC Class A
Angle	90°
Operating and Electrical	
Input Voltage	120 to 277 V
Input Frequency	50 to 60 Hz

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Material	Aluminum die-cast
Optic material	Glass
Optical cover/lens material	Glass
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [ 1 J]
Initial Performance (IEC Compliant)	
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	80

# Vaya Flood MP Medium

## Over Time Performance (IEC Compliant)

Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	100000
Lumen Maintenance 80% at 25°C Reported	60000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	74000
Lumen Maintenance 90% at 25°C Reported	60000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

## Application Conditions


Ambient temperature range	-40 to +104 °F
---------------------------	----------------

## Product Data

Full product code	871829138621699
Order product name	BCP435 3000 120-277 90 UL
EAN/UPC - Product	8718291386216
Order code	912400134045
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400134045
Net Weight (Piece)	5.580 kg



## Dimensional drawing



Vaya

