



Vaya Flood MP

BCP435 4000 120-277 90 UL

Very wide beam angle 90°

Vaya Flood MP gen2 is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Light source color	Neutral white		
Light source replaceable	No	Mechanical and Housing	
Driver included	Yes	Housing Material	Aluminum die cast
Optical cover/lens type	Tempered glass	Optic material	Glass
Luminaire light beam spread	90°	Optical cover/lens material	Glass
Protection class IEC	Safety class I	Optical cover/lens shape	Flat
UL mark	UL and cUL mark	Optical cover/lens finish	Clear
Optic type outdoor	Very wide beam angle 90°	Color	Dark gray
PSE mark	No	Approval and Application	
FCC mark	FCC Class A	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Angle	90°	Mech. impact protection code	IK06 [1 J]
Operating and Electrical		Initial Performance (IEC Compliant)	
Input Voltage	120 to 277 V	Init. Corr. Color Temperature	4000 K
Input Frequency	50 to 60 Hz		


Vaya Flood MP

Init. Color Rendering Index	82
Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	71000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	100000
Lumen Maintenance 80% at 25°C Reported	60000
Lumen Maintenance 80% at 40°C Calculated	45000
Lumen Maintenance 80% at 40°C Reported	45000
Lumen Maintenance 90% at 25°C Calculated	74000
Lumen Maintenance 90% at 25°C Reported	60000
Lumen Maintenance 90% at 40°C Calculated	23000
Lumen Maintenance 90% at 40°C Reported	23000

Application Conditions	
Ambient temperature range	-40 to +40 °C
Product Data	
Full product code	871829138623099
Order product name	BCP435 4000 120-277 90 UL
EAN/UPC - Product	8718291386230
Order code	912400134047
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400134047
Net Weight (Piece)	5.580 kg



Dimensional drawing



Vaya

