



eW Graze MX Powercore

eW Graze MX Powercore, 3000 K, 60° x 30° Beam Angle, 914 mm (3 ft)

eW Graze MX Powercore, 3000 K, 60° x 30° Beam Angle, 914 mm (3 ft)

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Product data

General information		Input frequency	
Lamp family code	LED-HB [LED High Brightness]	50 to 60 Hz	
Light source colour	White	Controls and dimming	
Light source replaceable	No	Dimmable	Yes
Luminaire light beam spread	60° x 30°	Mechanical and housing	
Protection class IEC	Safety class I	Housing material	Extruded aluminium
CE mark	CE mark	Optical cover/lens material	Polycarbonate
UL mark	UL and cUL mark	Length	914 mm
Lifetime to 50% luminous flux	60000 h	Approval and application	
Lifetime to 70% luminous flux	60000 h	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Operating and electrical		Mech. impact protection code	IK10 [20 J vandal-resistant]
Input Voltage	100 to 277 V		

eW Graze MX Powercore

Vibration standard	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
FCC mark	FCC Class A
Vibration rating	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.

Initial performance (IEC compliant)

Init. Corr. Colour Temperature	3000 K
Initial input power	42 W

Over time performance (IEC compliant)

Lumen Maintenance 50% at 25 °C	60000
Reported	
Lumen Maintenance 50% at 50 °C	60000
Reported	
Lumen Maintenance 70% at 25 °C	60000
Reported	

Lumen Maintenance 70% at 50 °C	60000
Reported	

Application conditions


Ambient temperature range	-20 to +50 °C
----------------------------------	---------------

Product data

Full product code	871829139583600
Order product name	BCS419 60x30-3000 L914
EAN/UPC – product	8718291395836
Order code	523-000080-74
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	912400135127
Net Weight (Piece)	3.800 kg
Commercial Code	523-000080-74
Catalogue number description	eW Graze MX Powercore, 3000 K, 60° x 30° Beam Angle, 914 mm (3 ft)



Dimensional drawing



BCS419 60x30-3000 L914

