



# eW Graze MX Powercore

## eW Graze MX Powercore, 3000 K, 10° x 60° Beam Angle, 1220 mm (4 ft)

eW Graze MX Powercore, 3000 K, 10° x 60° Beam Angle, 1220 mm (4 ft)

eW Graze MX Powercore is a high-performance, exterior linear luminaire that features the most light output in our line of solid white light grazing luminaires. It is designed to highlight architectural features ranging from surface textures and molding details to archways and windows. Graze Essential White luminaires offer a single channel of white light. Available in 2700 K, 3000 K, 3500 K, 4000 K, and 5500 K. Multiple luminaire lengths, beam angles, output levels, and power consumption levels support a large range of façade or surface illumination applications. Low-profile housing, connectorized cabling, a universal power input range, and direct line voltage operation make Graze luminaires easy to install and operate.

### Product data

General information		Operating and electrical	
Lamp family code	LED-HB [ LED High Brightness]	Input Voltage	100 to 277 V
Light source color	White	Input Frequency	50 to 60 Hz
Light source replaceable	No	Mechanical and housing	
Luminaire light beam spread	10° x 60°	Housing Material	Aluminum extruded
Protection class IEC	Safety class I	Optical cover/lens material	Polycarbonate
CE mark	CE mark	Length	1219 mm
UL mark	UL and cUL mark		
Lifetime to 70% luminous flux	60000 h		

eW Graze MX Powercore

Approval and application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Vibration Standard	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
Corrosion Resistance	Complies with ASTM B117 standard with special order. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
FCC mark	FCC Class A
Vibration Rating	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.

Initial performance (IEC compliant)	
Init. Corr. Color Temperature	3000 K
Initial input power	60 W

Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25°C	60000
Reported	
Lumen Maintenance 50% at 50°C	60000
Reported	

Lumen Maintenance 70% at 25°C	60000
Reported	
Lumen Maintenance 70% at 50°C	60000
Reported	

Application conditions	
Ambient temperature range	-20 to +50 °C

Product data	
Full product code	871829139585000
Order product name	BCS419 10x60-3000 L1219
EAN/UPC - Product	8718291395850
Order code	523-000080-76
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400135129
Net Weight (Piece)	4.700 kg
Catalog Number	523-000080-76
Catalog Number Description	eW Graze MX Powercore, 3000 K, 10° x 60° Beam Angle, 1220 mm (4 ft)



Dimensional drawing



