



ColorBurst IntelliHue Powercore

ColorBurst IntelliHue Powercore, 8° Native (no spread lens), Black Housing, Architectural

ColorBurst IntelliHue Powercore, 8° Native (no spread lens), Black Housing, Architectural

ColorBurst IntelliHue Powercore brings the precise control of colour and high-quality tunable white light in the same luminaire for outdoor wall-washing and spot-lighting applications. The IntelliHue technology delivers 80+ CRI (2,700 K to 4,000 K) and the ability to tint any CCT between 2,000 K and 10,000 K above and below the black-body curve.

Product data

General information		Light technical	
Beam angle of light source	8°	Efficacy (lm/W) @ 4,000 K	47.2 lm/W
Lamp colour code	IntelliHue	Efficacy (lm/W) @ 2,700 K	48.8 lm/W
Light source replaceable	No	CRI @ 4,000 K	85
Driver included	Yes	Operating and electrical	
Optical cover/lens type	GT [Tempered glass]	Input Voltage	100 to 277 V
Luminaire light beam spread	8°	Input frequency	50 to 60 Hz
Protection class IEC	Safety class I (I)	Controls and dimming	
CE mark	CE mark	Dimmable	Yes
Glare-shielding accessories	HC [Honeycomb louvre]	Mechanical and housing	
Glasses	No [-]	Housing configuration	BV [Basic version]
Angle	8°		

ColorBurst IntelliHue Powercore

Housing material	Aluminum die-cast
Colour	Black

Approval and application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK08 [5 J vandal-protected]
Vibration standard	Complies with ANSI C136.31, 3G
Vibration rating	Complies with ANSI C136.31, 3G
	887795

Initial performance (IEC compliant)

Initial luminous flux (system flux)	1481 lm
Initial LED luminaire efficacy	47 lm/W
Lamp colour temperature	- K
Colour Rendering Index	≥80
Initial input power	33 W

Over time performance (IEC compliant)

Lumen Maintenance 70% at 25 °C Calculated	48300
Lumen Maintenance 70% at 50 °C Calculated	48300
Lumen Maintenance 80% at 25 °C Calculated	48300

Lumen Maintenance 80% at 50 °C Calculated	48300
Lumen Maintenance 90% at 25 °C Reported	27000
Lumen Maintenance 90% at 50 °C Reported	25000

Application conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product data

Full product code	871869921147999
Order product name	BCP462 G2 19xLED-HB/RGBMW BK
EAN/UPC – product	8718699211479
Order code	423-000003-24
SAP numerator – quantity per pack	1
Numerator – packs per outer box	2
SAP material	912400135472
Net Weight (Piece)	6.800 kg
Commercial Code	423-000003-24
Commercial Code	ColorBurst IntelliHue Powercore, 8° Native (no spread lens), Black Housing, Architectural



Dimensional drawing



BCP462 G2 19xLED-HB/RGBMW BK

