



ColorBurst IntelliHue Powercore



ColorBurst IntelliHue Powercore, 8° Native (no spread lens), Bronze Housing, Landscape

ColorBurst IntelliHue Powercore, 8° Native (no spread lens), Bronze Housing, Landscape

ColorBurst IntelliHue Powercore produces high-quality white, pastel, and saturated color light, in the same precisely controllable luminaire for outdoor wall washing and spot lighting applications. IntelliHue technology delivers exceptional CRI and the ability to choose any CCT between 2000 K and 10000 K.

Product data

General information	
Beam angle of light source	8 °
Light source color	IntelliHue
Light source replaceable	No
Driver/power unit/transformer	-
Driver included	Yes
Optical cover/lens type	Tempered glass
Luminaire light beam spread	8°
Protection class IEC	Safety class I
CE mark	CE mark
Glare shielding accessories	Honeycomb louver
Glasses	-
Angle	8°

Light technical	
Efficacy (lm/W) @ 4000 K	46.9 lm/W
Efficacy (lm/W) @ 2700 K	49 lm/W
CRI @ 4000 K	85

Operating and electrical	
Input Voltage	100 to 277 V
Input Frequency	50 to 60 Hz

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Housing configuration	Housing with medium-length arm
Housing Material	Aluminum die cast

ColorBurst IntelliHue Powercore

Color	Bronze
-------	--------

Approval and application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK08 [5 J vandal-protected]
Corrosion Resistance	Complies with ASTM B117 standard for > 1,500 hours
EPREL Registration Number	887798

Initial performance (IEC compliant)

Initial luminous flux (system flux)	1481 lm
Initial LED luminaire efficacy	47 lm/W
Init. Corr. Color Temperature	- K
Init. Color Rendering Index	≥80
Initial input power	33 W

Over time performance (IEC compliant)

Lumen Maintenance 70% at 25°C Calculated	48300
Lumen Maintenance 70% at 50°C Calculated	48300
Lumen Maintenance 80% at 25°C Calculated	48300
Lumen Maintenance 80% at 50°C Calculated	48300

Lumen Maintenance 90% at 25°C Reported	27000
Lumen Maintenance 90% at 50°C Reported	25000

Application conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product data

Full product code	871869921150999
Order product name	BCP462 G2 19xLED-HB/RGBMW HMA BZ
EAN/UPC - Product	8718699211509
Order code	423-000003-29
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400135475
Net Weight (Piece)	3.470 kg
Catalog Number	423-000003-29
Catalog Number Description	ColorBurst IntelliHue Powercore, 8° Native (no spread lens), Bronze Housing, Landscape



Dimensional drawing



BCP462 G2 19xLED-HB/RGBMW HMA BZ

