



# ColorBurst Powercore gen2 RGBW/RGBA



## ColorBurst Powercore gen2, RGBW, 8° Native (no spread lens), White Housing, Architectural

ColorBurst Powercore gen2, RGBW, 8° Native (no spread lens), White Housing, Architectural

ColorBurst Powercore gen2 is a high-output, exterior-rated LED lighting luminaire designed for accent and site lighting. Architectural and landscape luminaires deliver full-colour light output of up to 1,293 lumens to support a range of dynamic uplighting, floodlighting and decorative lighting applications.

### Product data

General information	
Light source colour	RGBW
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	GT [ Tempered glass]
Luminaire light beam spread	8°
Protection class IEC	Safety class I
CE mark	CE mark
UL mark	UL and cUL mark
Glare-shielding accessories	GS [ Glare shield]
Operating and electrical	
Input Voltage	100 to 277 V
Input frequency	50 to 60 Hz

Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Colour	White
Approval and application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK08 [ 5 J vandal-protected]
Vibration standard	Complies with ANSI C136.31, 3G
Vibration rating	Complies with ANSI C136.31, 3G
	887805


ColorBurst Powercore gen2 RGBW/RGBA

Initial performance (IEC compliant)	
Initial luminous flux (system flux)	1230 lm
Initial LED luminaire efficacy	41 lm/W
Initial input power	30 W
Over time performance (IEC compliant)	
Lumen Maintenance 70% at 25 °C	48300
Calculated	
Lumen Maintenance 70% at 50 °C	48300
Calculated	
Application conditions	
Ambient temperature range	-40 to +50 °C
Product data	
Full product code	871869921157899

Order product name	BCP462 G2 19xLED-HB/RGBW WH
EAN/UPC – product	8718699211578
Order code	423-000004-27
SAP numerator – quantity per pack	1
Numerator – packs per outer box	2
SAP material	912400135482
Net Weight (Piece)	6.800 kg
Commercial Code	423-000004-27
Catalogue number description	ColorBurst Powercore gen2, RGBW, 8° Native (no spread lens), White Housing, Architectural



Dimensional drawing



BCP462 G2 19xLED-HB/RGBW WH

